



# RH SUPPORT

An RH chair is the perfect work tool, a chair that puts you in an optimal position all day, every day. A few simple adjustments is all it takes to make your RH chair fit your individual anatomy. RH chairs support an upright posture and active sitting, increasing your performance.

A series of work chairs designed for people who work in non-standard ways. Stay supported working at different heights or even "back to front". RH Support is available in various models so that you can customise your chair for your own needs. RH Support is also available as an ESD chair.

#### **Ergonomics**

Providing complete support in any working position, enabling you to always sit correctly and breathe properly.

- Seamless and separate adjustable seat and back angle.
- A user-friendly multiuser chair.
- Can be tailor-made to almost all tasks and environments. Choose between five different seats and two different back designs, five gas stems and foot-ring depending on needs and preferences.
- Especially developed for people who need the flexibility of easily switching between sitting and standing.

## Quality

• 10 year guarantee

Flokk is certified in accordance to:

- ISO 9001
- ISO 14001

RH Support is certified in accordance to:

• IEC 61340 (ESD)

### Environment

- Supports companies' environmental profile and credibility (CSR) -Cradle to cradle proof
- Easy to disassemble and no harmful chemicals
- ISO 14025 (EPD)
- GREENGUARD

#### Design

Materials and surfaces communicating comfort and wellbeing through bodyfitting forms. Expressing human performance.

## Fire classifications

Foams and standard fabrics are tested to BS/EN 1021–1&2 (cigarette & match). Foam and fabric according to BS-5852 ignition source 5 (crib 5) can be delivered on request. Please contact our customer service for further information.

## Maintenance

Vacuum clean the chair with a furniture brush or wipe it with a clean cloth or sponge slightly dampened with lukewarm clean water. Do not remove any plastic parts or attempt to open the seating mechanism. Contact your Flokk dealer if the chair requires servicing or maintenance.

See **flokk.com/rh** for RH Support interactive user instruction guide.















RH SUPPORT SADEL

RH SUPPORT TABURETT

RH SUPPORT LIMPAN

RH SUPPORT ALTERNATIV

#### CHAIR MODELS AVAILABLE:

## RH SUPPORT

- SADEL 4501
- TABURETT 4511
- LIMPAN 4521
- ALTERNATIV 4545

• 4532 - Polyurethane seat

• 4533 - Polyurethane seat

• ESD

If you select a version without a backrest, you can also choose as an option a simple mechanism that only adjusts the chair's height.

MEASUREMENTS	RH SUPPORT SADEL	RH SUPPORT TABURETT	RH SUPPORT LIMPAN	RH SUPPORT ALTERNATIV
Seat depth	380 mm	-	240 mm	380 mm
Seat width	410 mm	Ø 350 mm	450 mm	350 mm
Overall height standard	565-810 mm	580-825 mm	565-810 mm	580-825 mm
Backrest height	230 mm	230 mm	230 mm	260 mm
Backrest width	380 mm	380 mm	380 mm	220 mm
Diameter of base	590 mm	590 mm	590 mm	590 mm

#### OPTIONS

- Footring 6F
- 2 Base 5N, chrome-plated steel
- 3 Base 5F, grey lacquered aluminium
- Base 5F, polished aluminium
- Base 5F, black lacquered aluminium
- Base 5G, grey lacquered aluminium Base 5G, black lacquered aluminium
- 9 Castors 7D, for soft floors for base 5N
- 10 Castors 7HN, for hard floors for base 5N
- 11 Castors 7G, lock automatically under load
- 12 Castors for soft floors
- 13 Castors for hard floors

#### GAS STEMS

- E (standard), Silver or Black approx 565-810 mm\*
- D, Silver or Black, approx 485-665 mm\*
- A, Silver or Black, approx 415-545 mm\*
- B, Silver or Black, approx 375-510 mm\*
- 4FL, Black, approx 345-430 mm
- \* = Dimensions are for the RH Support 4501 model. See our price list for dimensions of other models.

For other options see the RH Price List.

The design and specifications of RH Chairs' products are developed on an ongoing basis and the above formulations should not be perceived as completely final.

## **ESD**

6

RH Support is available as an ESD chair. Flokk provides a 5 year warranty for ESD, conditional on castors and treads being cleaned regularly with a suitable cleaning agent.

The chairs are approved in line with IEC 61340(ESD). To work effectively the chair should be used in an ESD-adapted environment.